

ERGOLINE BEAUTY ANGEL– 235 volts, three phase, 30 amp (4 wire) circuit - Actual amp draw of 23 amps - This unit has approximately 6 ft. of # 8 AWG wire (3 hot, and 1 ground) coming out of the left side of the back panel through a 1-inch liquid-tight flex connector. This wire must be sleeved with flex and brought into a junction box. Do not shorten wire, as this additional length is necessary to move the bed for service. The wires should then be tied into a dedicated three phase, 30 amp (4 wire) circuit. Contact a licensed electrician. Check local code for disconnect requirements. **If 235 volts are not available buck/boost transformers will be required.** If three phase power is not available this unit can be converted to a single phase unit. The unit will then have approximately 6 ft. of # 4 AWG wire (2 hot, and 1 ground) coming out through the 1-inch liquid-tight flex connector. It will then require a 235 volt, 50 amp (3 wire) circuit – Actual amp draw of 40 amps. *All locations are given as if you were standing in front of the bed or unit.*



ROOM SIZE	NO. OF BODY LAMPS
6 X 8	30

LABOR WARRANTY: 90 DAYS

PARTS WARRANTY: 3 YEARS

BEAUTY ANGEL

Dimensions

B	1392 mm
B1	864 mm
B2	866 mm
B3	166 mm
B4	1367 mm
T	1279 mm
T1	1380 mm
T2	1837 mm
T3	865 mm
H	2341 mm
H1	69 mm
H2	2600 mm
H3	2020 mm
BK	1935 mm
BK1	500 mm
BK2	500 mm
TK	2400 mm
TK1	880 mm
TK2	300 mm

